







FOCAL LENGTH (EFL): 25,4 ±0,25

BACK FOCAL LENGTH (BFL): 20

SURFACE A			SURFACE B			SURFACE C			SURFACE D						
Øe 14			Øe 14			Øe 14			Øe 14						
			CEMENT: NOA 61 OR EQUIVALENT			CEMENT: NOA 61 OR EQUIVALENT									
PROTECTIVE CHAMFERS AS NEEDED						FIRST ANGLE PROJECTION		 Edmund Optics®							
ROHS: COMPLIANT		SCALE: NONE		λ = 587,6nm											
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY								TITLE		15mm Dia x 25,4mm EFL Hastings Triplet Achromatic Lens					
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								ALL DIMS IN:		mm					
INDICATIONS IN ACCORDANCE WITH ISO 10110								DWG NO		30120		SHEET SIZE A4		SHEET 1 OF 3	



LEFT SURFACE		MATERIAL	RIGHT SURFACE		
R 9,3±0,009 CX		GLASS N-F2 620/364	R 9,3±0,009 CX		
Øe 14			Øe 14		
3/ 3 (0,5) λ=632,8 nm			3/ 3 (0,5) λ=632,8 nm		
4/ -			4/ -		
5/ 40 - 20 (MIL-PRF-13830B)			5/ 40 - 20 (MIL-PRF-13830B)		
6/ -			6/ -		
PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	15mm Dia x 25,4mm EFL Hastings Triplet Achromatic Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			DWG NO	30120	SHEET SIZE A4
INDICATIONS IN ACCORDANCE WITH ISO 10110		ALL DIMS IN:	mm		

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	$\lambda = 587.6\text{nm}$			TITLE	15mm Dia x 25,4mm EFL Hastings Triplet Achromatic Lens	
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm		DWG NO	30120	SHEET SIZE A4
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING							
INDICATIONS IN ACCORDANCE WITH ISO 10110							