

TECHSPEC® HPI SERIES

FIXED FOCAL LENGTH LENSES

#36-747 • 8.5mm • f/1.8

Designed for instrumentation imaging applications, TECHSPEC® HPI Series Fixed Focal Length Lenses offer a variety of fixed aperture options and up to 9 MP resolution. The simplified mechanical components allow for a compact size and cost reduction, making them ideal for a variety of applications. An adjustable, lockable focus feature allows for setting and locking the best focus position for instrumentation integration.



Focal Length:	8.5mm
Working Distance¹:	75mm - ∞
Max. Sensor Format:	2/3"
Camera Mount:	C-Mount
Aperture (f/#):	f/1.8
Distortion %²:	<7.77%
Object Space NA²:	0.024864

Magnification Range:	0X - 0.092X
Type:	Fixed Focal Length Lens
Length:	44.57mm
Weight:	84g
RoHS:	Compliant
Number of Elements (Groups):	9 (8)
AR Coating:	425 - 675nm BBAR

1. From front housing 2. At Minimum W.D.

At Minimum W.D. (75mm)						
Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"
Field Of View³	39.6mm - 24.1°	53.2mm - 32.0°	64.8mm - 38.4°	71.9mm - 42.2°	81.5mm - 47.2°	101.4mm - 56.8°

3. Horizontal FOV on Standard (4:3) sensor format. Min W.D.




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/1.8
WD: 167mm
HORIZONTAL FOV: 200mm




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

© COPYRIGHT 2019 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

MTF & DOF: f/1.8
WD: 444mm
HORIZONTAL FOV: 500mm




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

© COPYRIGHT 2019 EDMUND OPTICS, INC. ALL RIGHTS RESERVED