




NOTES:

- 1. SUBSTRATE: PMMA
- 2. COATING
S1 & S2: R(AVG) < 0.5% @ 450 - 650nm
- 3. FOCAL LENGTH TOLERANCE: ±1%



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	12.7mm DIA. f/4 VIS COATED, MOLDED ACRYLIC ASPHERIC LENS	
SHAPE	CONVEX	PLANO			DWG NO		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	48178	SHEET 1 OF 1