





FOCAL LENGTH (EFL): 1000 ±10
 BACK FOCAL LENGTH (BFL): 997,59

- 1 1064nm Laser AR Coating
 R(ABS) < 0,25% @ 1064nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 476,089 CX Øe 11,7 (λ) SEE NOTE 1 3/ 2 (0,2) λ=632,8 nm 4/ - 5/ 10 - 5 6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]	GLASS Fused Silica 458/678	R ∞ PL Øe 11,7 (λ) SEE NOTE 1 3/ 2 (0,2) λ=632,8 nm 4/ 2,18' 5/ 10 - 5 6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 355nm			TITLE	12,7mm Dia x 1000mm FL, 1064nm Laser AR Coating, 15J Coated, Plano-Convex Lens	
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm			DWG NO	38743
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				SHEET SIZE A4	SHEET 1 OF 1		
INDICATIONS IN ACCORDANCE WITH ISO 10110							