




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]


	S1	S2	THIRD ANGLE PROJECTION 		TITLE	M25.5 X 0.50, MOUNTED THREADED, RED FILTER	
SHAPE	PLANO	PLANO			ALL DIMS IN	mm	DWG NO
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]


	S1	S2	THIRD ANGLE PROJECTION 		TITLE	M25.5 X 0.50, MOUNTED THREADED, GREEN FILTER	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	46543	SHEET 1 OF 1
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] **Edmund Optics**[®]

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	M25.5 X 0.50, MOUNTED THREADED, BLUE FILTER	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	46544	SHEET 1 OF 1
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY






REV. A	VALUE
POLARIZATION EFFICIENCY	95%
TRANSMISSION	SINGLE: 30%; CROSSED: 0.15%

THIRD ANGLE PROJECTION	
ALL DIMS IN	mm


TITLE	M25.5 x 0.5 MOUNTED LINEAR GLASS POLARIZING FILTER
DWG NO	46575
SHEET	1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



REV. A	VALUE
SHAPE	PLANO
CUT-ON WAVELENGTH	390
SURFACE FLATNESS	4 - 6λ
SURFACE QUALITY	80-50
CLEAR APERTURE	Ø21



EO® **Edmund Optics**®

TITLE	M25.5 X 0.5 MOUNTED, UV CUT-OFF FILTER
DWG NO	46577
SHEET	1 OF 1


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY





REV. A	VALUE
CUT-ON WAVELENGTH	N/A
CUT-OFF WAVELENGTH	<750nm
SURFACE QUALITY	60-40

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

TITLE	M25.5 X 0.5 MOUNTED IR CUT-OFF FILTER
DWG NO	49800
SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



REV. A	VALUE
CUT-ON WAVELENGTH	390nm
CUT-OFF WAVELENGTH	690nm
SURFACE QUALITY	60-40






ALL DIMS IN mm

TITLE	M25.5 X 0.5 MOUNTED UV/IR CUT-OFF FILTER
DWG NO	49808
SHEET 1 OF 1	

NOTES:


1. SUBSTRATE:
ND Filter Glass
2. OPTICAL DENSITY: 0.3
3. COATING SPECIFICATION:
AR Coating: MgF₂
R(AVG) ≤ 1.75% @ 400 - 700nm
4. TRANSMISSION (%): 50
5. FILTER THREAD: M25.5 x 0.5

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY






	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50

THIRD ANGLE PROJECTION	TITLE	FILTER ND MTD 0.3OD 25.5X0.5	
ALL DIMS IN mm	DWG NO	59163	SHEET 1 OF 1

NOTES:


1. SUBSTRATE:
ND Filter Glass
2. OPTICAL DENSITY: 0.6
3. COATING SPECIFICATION:
AR Coating: MgF2
R(AVG) ≤ 1.75% @ 400 - 700nm
4. TRANSMISSION (%): 25
5. FILTER THREAD: M25.5 x 0.5

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY






	S1	S2	THIRD ANGLE PROJECTION		TITLE	FILTER ND MTD 0.6OD 25.5X0.5	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	59168	SHEET 1 OF 1
SURFACE QUALITY	80-50	80-50					

NOTES:


1. SUBSTRATE:
ND Filter Glass
2. OPTICAL DENSITY: 0.9
3. COATING SPECIFICATION:
AR Coating: MgF2
R(AVG) ≤ 1.75% @ 400 - 700nm
4. TRANSMISSION (%): 12.5
5. FILTER THREAD: M25.5 x 0.5

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**






SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION		TITLE	FILTER ND MTD 0.9OD 25.5X0.5	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	59173	SHEET 1 OF 1
SURFACE QUALITY	80-50	80-50					

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



REV. A	VALUE
CUT-ON WAVELENGTH	720nm
CUT-OFF WAVELENGTH	2750nm
SURFACE QUALITY	80-50



ALL DIMS IN mm

TITLE	M25.5 X 0.5 MOUNTED UV/VIS CUT-OFF FILTER (R-72)
DWG NO	65796
SHEET	1 OF 1