




NOTES:

- 1. SUBSTRATE:
D-ZK3
- 2. NUMERICAL APERTURE: 0.54
- 3. COATING
S1 & S2: R(ABS) <1.0% @ 600 - 1050nm
- 4. FOCAL LENGTH TOLERANCE: ±1%
- 5. TRANSMITTED WAVEFRONT ERROR (λ, RMS @ 632.8NM): <0.087
- 6. DESIGN WAVELENGTH: 633nm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	6.75	 Edmund Optics®		
			WD	4.30			
SHAPE	CONVEX	PLANO			TITLE	LightPath 354115 9.2mm Dia., 0.54 NA, BBAR (600-1050nm), Molded Aspheric Lens	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	Ø7.00	Ø5.30	ALL DIMS IN	mm	DWG NO	16692	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					