




- NOTES:
- 1. SUBSTRATE:
D-ZLAF52LA
 - 2. NUMERICAL APERTURE:
OBJECT: 0.12
IMAGE: 0.50
WD, OBJECT (mm): 3.93
WD, IMAGE (mm): 0.70
 - 3. COATING
S1 & S2: R(ABS) <1.0% @ 600 - 1050nm
 - 4. FOCAL LENGTH TOLERANCE: $\pm 1\%$
 - 5. TRANSMITTED WAVEFRONT ERROR (λ , RMS @ 632.8NM): <0.700
 - 6. DESIGN WAVELENGTH: 1550nm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	0.80	 Edmund Optics®		
			WD	0.70			
SHAPE	CONVEX	PLANO			TITLE	LightPath 355915 1.3mm Dia., 0.50 NA, BBAR (600-1050nm), Molded Aspheric Lens	
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	$\phi 1.00$	$\phi 0.77$	ALL DIMS IN	mm	DWG NO	16698	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					