

NOTES:

1. SUBSTRATE:
SCHOTT NG11

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 0.1

5. TRANSMISSION (%): 79.4

6. ROHS COMPLIANT




NEUTRAL DENSITY FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY







Edmund Optics®

	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG11, 0.1 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16718	SHEET 1 OF 1

NOTES:

- 1. SUBSTRATE:
SCHOTT NG11
- 2. FINE GRIND SURFACE
- 3. COATING SPECIFICATION:
S1 & S2:NONE
- 4. OPTICAL DENSITY: 0.15
- 5. TRANSMISSION (%): 70.79
- 6. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	SCHOTT NG11, 0.15 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50	ALL DIMS IN	mm	DWG NO	16661	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					

NOTES:

1. SUBSTRATE:
SCHOTT NG11

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 0.2


5. TRANSMISSION (%): 63.1

- ## 6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY







	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG11, 0.2 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16721	SHEET 1 OF 1

NOTES:


- 1. SUBSTRATE:
SCHOTT NG11
- 2. FINE GRIND SURFACE
- 3. COATING SPECIFICATION:
S1 & S2:NONE
- 4. OPTICAL DENSITY: 0.3
- 5. TRANSMISSION (%): 50.11
- 6. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY







	S1	S2	THIRD ANGLE PROJECTION 				TITLE SCHOTT NG11, 0.3 OD, 25mm DIA., ABSORPTIVE ND FILTER		DWG NO 16662	SHEET 1 OF 1
SHAPE	PLANO	PLANO								
SURFACE QUALITY	80-50	80-50	ALL DIMS IN		mm					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED								

NOTES:

- 1. SUBSTRATE:
SCHOTT NG4
- 2. FINE GRIND SURFACE
- 3. COATING SPECIFICATION:
S1 & S2:NONE
- 4. OPTICAL DENSITY: 0.4
- 5. TRANSMISSION (%): 39.8
- 6. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY





Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	SCHOTT NG4, 0.4 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50	ALL DIMS IN	mm	DWG NO	16724	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					

NOTES:

- 1. SUBSTRATE:
SCHOTT NG4
- 2. FINE GRIND SURFACE
- 3. COATING SPECIFICATION:
S1 & S2:NONE
- 4. OPTICAL DENSITY: 0.5
- 5. TRANSMISSION (%): 31.6
- 6. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY





Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	SCHOTT NG4, 0.5 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50	ALL DIMS IN	mm	DWG NO	16727	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					

NOTES:


- 1. SUBSTRATE:
SCHOTT NG4
- 2. FINE GRIND SURFACE
- 3. COATING SPECIFICATION:
S1 & S2:NONE
- 4. OPTICAL DENSITY: 0.6
- 5. TRANSMISSION (%): 25.11
- 6. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 				TITLE SCHOTT NG4, 0.6 OD, 25mm DIA., ABSORPTIVE ND FILTER		DWG NO 16663	SHEET 1 OF 1
SHAPE	PLANO	PLANO								
SURFACE QUALITY	80-50	80-50	ALL DIMS IN		mm					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED								

NOTES:

1. SUBSTRATE:
SCHOTT NG4

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 1.0


5. TRANSMISSION (%): 10.0

- ## 6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	SCHOTT NG4, 1.0 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16664	SHEET 1 OF 1

NOTES:

1. SUBSTRATE:
SCHOTT NG4

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 1.3


5. TRANSMISSION (%): 5.01

- ## 6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG4, 1.3 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16665	SHEET 1 OF 1

NOTES:

1. SUBSTRATE:
SCHOTT NG9

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 1.6


5. TRANSMISSION (%): 2.51

6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG9, 1.6 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16666	SHEET 1 OF 1

NOTES:

1. SUBSTRATE:
SCHOTT NG9

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 2.0


5. TRANSMISSION (%): 1.0

6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY







	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG9, 2.0 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16667	SHEET 1 OF 1

NOTES:

- 1. SUBSTRATE:
SCHOTT NG9
- 2. FINE GRIND SURFACE
- 3. COATING SPECIFICATION:
S1 & S2:NONE
- 4. OPTICAL DENSITY: 3.0
- 5. TRANSMISSION (%): 0.1
- 6. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	SCHOTT NG9, 3.0 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50	ALL DIMS IN	mm	DWG NO	16670	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					

NOTES:

1. SUBSTRATE:
SCHOTT NG9

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING


2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE


4. OPTICAL DENSITY: 4.0

5. TRANSMISSION (%): 0.01


6. ROHS COMPLIANT



$\varnothing 25.00_{\pm 0.38}$



Technical drawing of a vertical plate. The top width is dimensioned as 2.80 NOMINAL. Two arrows point inward from the top edge towards the centerline, labeled S1 and S2. A horizontal dashed line indicates the centerline. At the bottom, there is a triangle symbol containing the number 2.




NEUTRAL DENSITY FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY







Edmund Optics®

	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG9, 4.0 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16673	SHEET 1 OF 1

NOTES:

1. SUBSTRATE:
SCHOTT NG9
2. FINE GRIND SURFACE
3. COATING SPECIFICATION:
S1 & S2:NONE
4. OPTICAL DENSITY: 5.0
5. TRANSMISSION (%): 0.001
6. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

	S1	S2	THIRD ANGLE PROJECTION		TITLE	SCHOTT NG9, 5.0 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50	ALL DIMS IN	mm	DWG NO	16676	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					