




- NOTES:
- 1. SUBSTRATE: B270
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE
S3: NONE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	S3
SHAPE	PLANO	PLANO	PLANO
RADIUS	∞	∞	ASPHERIC
SURFACE QUALITY	160-50	80-50	160-50
CLEAR APERTURE	Ø 4.26	Ø 10.70	N/A
BEVEL	PROTECTED AS NEEDED		NONE

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	45° 5mm Output Dia., Molded Compound Parabolic Concentrator	
DWG NO	17710	SHEET 1 OF 1