


NOTES:

- 1. SUBSTRATE:
H-K51
- 2. COATING (APPLY ACROSS CLEAR APERTURE)



S1 & S2: MgF2 (400-700nm)
R(AVG) ≤ 1.75% @ 400 - 700nm

- 3. CENTERING: ≤30 ARCMIN



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	16.00	 Edmund Optics®	
			BFL @ 587.6nm	7.3		
SHAPE	CONVEX	CONVEX			TITLE	25.4mm Dia. x 16mm FL, MgF2 Coated, Aspheric Condenser Lens
SURFACE QUALITY	80-50 (typical)	80-50 (typical)			ALL DIMS IN	mm
CLEAR APERTURE	Ø 22.86	Ø 22.86				SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				