




FOCAL LENGTH (EFL): 50 ±0,5
BACK FOCAL LENGTH (BFL): 47,3

- 1 1064nm Laser AR Coating
R(ABS) < 0,25% @ 1064nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 23,804 CX Øe 11,7 (λ) SEE NOTE 1 3/ 2 (0,2) λ=632,8 nm 4/ - 5/ 10 - 5 6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]	GLASS Fused Silica 458/678	R ∞ PL Øe 11,7 (λ) SEE NOTE 1 3/ 2 (0,2) λ=632,8 nm 4/ 2,18' 5/ 10 - 5 6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 355nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



[®] Edmund Optics[®]

TITLE

12,7mm Dia x 50mm FL, 1064nm Laser
AR Coating, 15J Coated, Plano-Convex
Lens

DWG NO

38735

SHEET
SIZE A4

SHEET
1 OF 1