



- NOTES:
- 1. SUBSTRATE: N-BK7
 - 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
 - 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: VIS 0° (425-675nm)
S2: VIS 0° (425-675nm)
Ravg ≤0.4% @ 425 - 675nm

4. FINE GRIND SURFACE


- 5. ROHS COMPLIANT
- 6. TRANSMITTED WAVEFRONT (P-V):
λ/4 (per inch over clear aperture)




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø 11.25	Ø 11.25
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

**Edmund Optics®**

THIRD ANGLE
PROJECTION



ALL DIMS INmm

TITLE

12.5mm Dia., 1mm Thick, VIS 0° Coated
λ/4 N-BK7 Window

DWG NO

23380

SHEET
18 OF 84