





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	355
FULL WIDTH HALF MAX (FWHM)	53
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION





ALL DIMS IN

mm

Edmund Optics®

TITLE	SCHOTT UG-1 (UV) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	46048	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	493
FULL WIDTH HALF MAX (FWHM)	160
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	SCHOTT BG-18 (VIS) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	46052	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	526
FULL WIDTH HALF MAX (FWHM)	120
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	SCHOTT VG-9 (VIS) 50.8mm Square, Colored Glass Bandpass Filter	
DWG NO	46054	SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	470
FULL WIDTH HALF MAX (FWHM)	271
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	SCHOTT BG-38 (VIS) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	46434	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	330
FULL WIDTH HALF MAX (FWHM)	140
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	HOYA U-330 (UV) 50.8mm Square, Colored Glass Bandpass Filter	
DWG NO	46438	SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	340
FULL WIDTH HALF MAX (FWHM)	85
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	HOYA U-340 (UV) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	46440	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	360
FULL WIDTH HALF MAX (FWHM)	45
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	HOYA U-360 (UV) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	46442	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	830
FULL WIDTH HALF MAX (FWHM)	260
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	HOYA RT-830 (IR) 50.8mm Square, Colored Glass Bandpass Filter	
DWG NO	46444	SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	356
FULL WIDTH HALF MAX (FWHM)	146
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	SCHOTT BG-3 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	48638	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	370
FULL WIDTH HALF MAX (FWHM)	100
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	HOYA B-370 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter	
DWG NO	48639	SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY





	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	390
FULL WIDTH HALF MAX (FWHM)	125
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 Edmund Optics®	
TITLE	HOYA B-390 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter
DWG NO	48640
SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	440
FULL WIDTH HALF MAX (FWHM)	85
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	HOYA B-440 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter	
DWG NO	48641	SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	507
FULL WIDTH HALF MAX (FWHM)	210
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	SCHOTT BG-39 (VIS) 50.8mm Square, Colored Glass Bandpass Filter	
DWG NO	48642	SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	318
FULL WIDTH HALF MAX (FWHM)	175
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	SCHOTT UG-5 (UV) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	84898	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	325
FULL WIDTH HALF MAX (FWHM)	110
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	SCHOTT UG-11 (UV) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	84900	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	400
FULL WIDTH HALF MAX (FWHM)	150
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	SCHOTT BG-25 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter		
DWG NO	84902	SHEET 1 OF 1	

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	883
FULL WIDTH HALF MAX (FWHM)	315
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED





THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	SCHOTT RG-9 (IR) 50.8mm Square, Colored Glass Bandpass Filter	
DWG NO	84904	SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	480
FULL WIDTH HALF MAX (FWHM)	260
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	SCHOTT BG-42 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter	
DWG NO	84906	SHEET 1 OF 1