


## NOTES:

- 1. SUBSTRATE: UV GRADE FUSED SILICA
- COATING (APPLY ACROSS CLEAR APERTURE)
   \$1 & \$2: R(ABS) < 0.25% @ 532nm</li>
   R(ABS) < 0.25% @ 1064nm</li>
   R(AVG) < 1.0% @ 500 1100nm</li>
- 3. SURFACE S2 TO BE PARALLEL WITH S1 TO <5 ARCSEC
- 4. FINE GRIND SURFACE
- 5. Rohs Compliant







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO 20-10 Ø32.00			
SURFACE QUALITY	20-10				
CLEAR APERTURE	Ø32.00				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

THIRD ANGLE PROJECTION	$\phi$	TITLE
ALL DIMS IN	mm	DWG

B	Edmund Optics®
TITLE	40mm DIA., 4mm THICK, YAG-BBAR COATED, λ/10 FUSED SILICA WINDOW
	OUTET

S IN	mm	DWG NO	13358	SHEET 1 OF 1