NOTES:

- 1. SUBSTRATE: SAPPHIRE (AL2O3)
- 2. SURFACE \$1 TO BE PARALLEL WITH SURFACE \$2 TO WITHIN ≤3.5 ARCMIN
- 3. ENVIRONMENTAL REQUIREMENTS:

\$1 & \$2: HIGH DURABILITY BBAR (2000-5000nm) ADHESION: PER MIL-M-13508C PARA 4.4.6 ABRASION: SEVERE PER MIL-C-675C PARA 4.5.10

HUMIDITY: PER MIL-C-675C PARA 4.5.8 SALT SOLUBILITY: PER MIL-C-675C PARA 4.5.7 SALT SPRAY: PER MIL-C-675C PARA 4.5.9

TEMPERATURE CYCLE: PER MIL-M-13508C PARA 4.4.4


4. REFLECTION PERFORMANCE ACROSS CLEAR APERTURE ON CENTER


S1 & S2:

R(AVG) <1.5% @ 2000 - 5000nm R(ABS) <2.0% @ 2000 - 5000nm

FINE GRIND SURFACE

6. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

> SHEET 1 OF 1

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	Ø 22.50	Ø 22.50
SURFACE FLATNESS	2λ (typical)	2λ (typical)
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

			Edmund Optic	S®
THIRD ANGLE PROJECTION		TITLE	25mm Dia., 0.5mm Thick, 2000-5000nm Durability AR Coated Sapphire Wind	_
ALL DIMS IN	mm	DWG NO	18471	SHEET 1 OF 1