



NOTES:

- 1. SUBSTRATE:
OPTICAL GRADE GLASS
- 2. BANDWIDTH: 15nm
- 3. BLOCKING WAVELENGTH RANGE: 330 - 900nm
- 4. MINIMUM TRANSMISSION (%): >93 @ 482.5 – 497.5nm
- 5. ROHS COMPLIANT

NOTE: ARROW ON RING INDICATES PREFERRED DIRECTION OF PROPAGATION OF LIGHT.



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
CONE HALF ANGLE (°)	7	7
OPTICAL DENSITY OD (AVERAGE)	>5	>5
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	≥ Ø 10.00	≥ Ø 10.10
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	490nm CWL, >OD5, 20nm FWHM Bandpass Filter, 25mm Dia.		
DWG NO	78425	SHEET 16 OF 52	