





f': 10 ±0,1

BACK FOCAL LENGTH (BFL): 8,1



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,17 CX			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL		
Øe 6,3				Øe 6,3		
⌒ AR Rave(425nm - 675nm, 0°) ≤ 0,40%				⌒ AR Rave(425nm - 675nm, 0°) ≤ 0,40%		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ 5,8'				4/ -		
5/ 40 - 20				5/ 40 - 20		
6/ -				6/ -		
P				P		
PROTECTIVE CHAMFERS AS NEEDED			EO[®] Edmund Optics[®] TITLE 7mm Dia x 10mm FL, VIS 0 Coated, Plano-Convex Lens DWG NO 71301 SHEET SIZE A4 SHEET 1 OF 1			
ROHS: COMPLIANT						SCALE: NONE
λ = 587,6nm			FIRST ANGLE PROJECTION			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			⊕			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm			
INDICATIONS IN ACCORDANCE WITH ISO 10110						