

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Industrial and Pointing Lasers](#)

Laboratory Laser Diode Modules



- Visible and Near IR Models
- Focusable from 20mm to Infinity



Common Specifications

General

Note:	Includes: Users Manual, Power Supply, Warning Label, and Focus Key	Type of Laser:	Diode
--------------	--	-----------------------	-------

Optical Properties

Beam Size at Nearest Focus (µm):	25	Beam Diameter (mm):	4 x 2
Beam Divergence (mrad):	<0.5	Focus Range (mm):	35mm - ∞

Hardware & Interface Connectivity

Power Supply:	110/240 V AC (included)	Output Type:	Free Space
----------------------	-------------------------	---------------------	------------

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Beam Size at Nearest Focus (μm)	Beam Diameter (mm)	Beam Divergence (mrad)	Stock Number	Price	Buy
635.00	1 (Maximum)	25	4 x 2	<0.5	#53-227	£265.00	1 In Stock
670.00	3 (±5%)	25	4 x 2	<0.5	#39-569	£227.00	4 In Stock
850.00	3 (±5%)	25	4 x 2	<0.5	#53-760	£303.00	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com