

[All Products](#) /
 [Imaging Lenses](#) /
 [Zoom & Variable Magnification Lenses](#) /
 [Zoom Lenses](#)

TECHSPEC® M Series Variable Magnification Lenses



- Variable Magnification Lens
- Up to 5 MegaPixels, 3.45m Pixel Size Sensors
- 2/3", C-Mount Lens

Common Specifications

Physical & Mechanical Properties

Iris Option: Variable

Optical Properties

Resolution: 75 lp/mm @ >20%

Maximum Image Circle (mm): 11.00

Number of Elements (Groups): 5 (4)

Coating Specification: $\lambda/4$ MgF₂ @ 550nm

Sensor

Maximum Sensor Format: 2/3"

Threading & Mounting

Filter Thread: M25.5 x 0.50 (Female)

Mount: C-Mount

Technical Information

Products

Title	Stock Number	Price	Buy
0.5X M Series Fixed Magnification Non-Telecentric Lens	#87-531	£425.00	4 In Stock
0.75X M Series Fixed Magnification Non-Telecentric Lens	#87-532	£425.00	16 In Stock
1.0X M Series Fixed Magnification Non-Telecentric Lens	#87-533	£425.00	11 In Stock
0.5X - 1.0X M Series Non-Telecentric Lens	#87-535	£552.50	11 In Stock
0.15X - 0.5X M Series Non-Telecentric Lens	#87-536	£552.50	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com