

Optotune -2 to +3 Diopter, M26 x 0.706 to M26 x 0.706 Focus Tunable Lens | EL-16-40-TC-VIS-5D-M26

See More by [Optotune](#)



Stock **#35-087** CLEARANCE CONTACT US

-

1

+

£926²⁴

ADD TO CART

Volume Pricing	
Qty 1+	£926.24 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Specialty Lens

Type:

#88-940	Driver:
1,000,000,000	Lifecycles:
EL-16-40-TC-VIS-5D-M26	Model Number:
5 (typical @ 30°C)	Response Time (ms):
25 (typical @ 30°C)	Settling Time (ms):
Physical & Mechanical Properties	
16.00	Clear Aperture CA (mm):
47.0 x 70.0	Dimensions (mm):
17.60	Thickness (mm):
Optical Properties	
Low Dispersion Polymer	Substrate: □
BBAR (420-950nm)	Coating:
420 - 950	Wavelength Range (nm):
100.00	Abbe Number (v _d):
-2 to +3 diopter -500 to +333mm	Focus Range (mm):
1.3	Index of Refraction (n _d):
Transmitted Wavefront Error, RMS: Vertical: 0.25λ @ 525nm Horizontal: 0.50λ @ 525nm	
Electrical	
-250 to 250	Current (mA):
0 - 0.7	Power Consumption (W):
Threading & Mounting	
M26 x 0.706 (Male) M26 x 0.706 (Female)	Mounting Threads:
Environmental & Durability Factors	
-20 to +65	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Multiple Imaging Lens Mounting Options
- Large Clear Aperture Ideal for Machine Vision Applications
- Industrial Hirose Connection with Temperature Sensing
- Integrated Temperature Control for Improved Thermal Effects
- Optotune Focus Tunable Lenses 10mm Clear Aperture Hirose Connector and Lens Drivers Also Available

Optotune Focus Tunable Lenses 16mm Clear Aperture Hirose Connector eliminate the need for optomechanical subsystems otherwise required to alter the focal length of your imaging application. They feature large clear apertures and are offered in many popular machine vision mounting options, making them ideal for inspection and detection systems. These lenses offer continuous focusability from -2 to +3 diopters controlled by an industrial Hirose connection. Optotune Focus Tunable Lenses 16mm Clear Aperture Hirose Connector exhibit no autofluorescence, reducing unwanted light on the detector and feature integrated temperature sensing to provide open loop reproducibility typically within 0.1 diopters. The lenses are made of low dispersion polymer and feature a broadband anti-reflection coating.

Note: Hirose cables, available in 1m length (#88-941), 3m length (#33-468) or 5m length (#23-852), and Lens Driver (#88-940) are required and sold separately. The Gardasoft TR-CL180 Industrial Lens Controller (#13-803) is an optional accessory that provides repeatable, precision control of Optotune Industrial Focus-Tunable Lenses. Prescription data is available to model the effect an offset lens has on overall focal range.

TECHNICAL INFORMATION

