

[See all 12 Products in Family](#)

(0-1" Range), 0.0001", Spherical Micrometer, Spherical Anvil Flat Spindle, Ratchet Stop

See More by [Mitutoyo](#)



Stock **#78-332** **1 In Stock**

-

1

+

£228⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£228.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads	
±0.0001	Accuracy (inches):
General	
0 - 1 inches	Range:
295-153	Model Number:

Physical & Mechanical Properties

0.0001	Graduation (inches):
--------	----------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mike Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.