

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Ultrafast Laser Mirrors](#)

UltraFast Innovations (UFI) 780 and 800nm Highly-Dispersive Ultrafast Mirrors

See More by [UltraFast Innovations \(UFI\)](#)



- Reflection >99.8% (P-polarization) at 720 – 840nm or 780 – 830nm
- Low Group Delay Dispersion at 5° or 20° AOs
- Ideal for Pulse Compression of Ti:sapphire Ultrafast Lasers
- [Low GDD Mirrors](#) Also Available

Common Specifications



Physical & Mechanical Properties

Wedge Angle (arcmin):	10 ±5	Clear Aperture (%):	80
Back Surface:	Commercial Polish	Thickness (mm):	6.35 ±0.20

Optical Properties

Irregularity (P-V) @ 632.8nm:	$\lambda/10$	Coating Type:	Dielectric
Substrate:	Fused Silica (Corning 7980)		

Technical Information



Products

Wavelength Range (nm)	DWL (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
780 - 830	800	12.70	6.35	5	#12-330	£350.20 Volume Pricing	9 In Stock
720 - 840	780	25.40	6.35	20	#17-067	£669.76 Volume Pricing	5 In Stock
780 - 830	800	25.40	6.35	5	#12-331	£577.83 Volume Pricing	14 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com