

[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Plate Beamsplitters](#)

Infrared (IR) Pellicle Beamsplitters



- 45/55 Average R/T Ratio from 3 - 5 μ m
- No Ghost Images from Second Surface Reflections
- Eliminate Beam Displacement
- [Pellicle Beamsplitters](#) for the VIS-NIR Also Available

Common Specifications




Physical & Mechanical Properties

Construction:	Pellicle	Housing:	Black Anodized Aluminum
Thickness (μm):	2 +0.3/-0.2		

Optical Properties

Coating:	Dielectric		
Coating Specification:	45/55 @ 3000 - 5000nm	Index of Refraction (n_d):	1.5
Reflection/Transmission Ratio (R/T):	45/55	Substrate:	Nitrocellulose
Surface Quality:	40-20	Wavelength Range (nm):	3000 - 5000

Technical Information



Products

Dia. (mm)	CA (mm)	Substrate	Reflection/Transmission Ratio (R/T)	Wavelength Range (nm)	Stock Number	Price	Buy
19.05	12.7	Nitrocellulose	45/55	3000 - 5000	#19-280	£206.62 Volume Pricing	2 In Stock
34.90	25.4	Nitrocellulose	45/55	3000 - 5000	#19-281	£212.75 Volume Pricing	Contact Us
63.50	50.8	Nitrocellulose	45/55	3000 - 5000	#19-282	£277.53 Volume Pricing	Contact Us
88.90	76.2	Nitrocellulose	45/55	3000 - 5000	#19-283	£355.45 Volume Pricing	1 In Stock
114.30	101.6	Nitrocellulose	45/55	3000 - 5000	#19-284	£560.32 Volume Pricing	6 In Stock
165.10	152.4	Nitrocellulose	45/55	3000 - 5000	#19-285	£923.65 Volume Pricing	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com