

[See all 12 Products in Family](#)

(0-13mm Range), 0.01mm Increment, Metric Micrometer Head

See More by [Mitutoyo](#)



Stock **#78-313** **1 In Stock**

-

1

+

£70⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£70.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads	
General	
0 - 13mm	Range:
148-801-10	Model Number:
Physical & Mechanical Properties	
±2	Accuracy (µm):

Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mike Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.