

[See all 24 Products in Family](#)

TECHSPEC®

0.18X 1/2" GoldTL™ Telecentric Lens



#58-258 (0.18X)

Stock **#58-258** 20+ In Stock

-

1

+

£1,844⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,844.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
GoldTL™ Series	Series:
Telecentric Lens	Type:
Focusable Telecentric	Special Type of Lens:
Stock No. of Mounting Clamp: #56-026 Sold Separately	


Physical & Mechanical Properties	
Variable	Iris Option:
196.30	Length (mm):
196.30	Length excluding Threads (mm):
79.00	Maximum Diameter (mm):
1.45	Weight (kg):
Optical Properties	
35.6mm	Horizontal Field of View, 1/2" Sensor:
8.00	Maximum Image Circle (mm):
0.015	Numerical Aperture NA, Object Side:
>60% @ 40 lp/mm	Resolution, Image Space MTF @ f/10:
10 (7)	Number of Elements (Groups):
<0.040	Typical Telecentricity @ 588nm (°):
0.045	Typical Distortion @ 588nm (%):
0.18X	Primary Magnification PMAG:
0.18	Telecentric Lens Magnification:
161 - 186	Working Distance (mm):
35.6 x 26.7	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/18	Aperture (f/#):
N/4 MgF ₂	Coating:
±15.5 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.18X	Magnification:
VIS	Lens Wavelength Range:
Sensor	
1/2"	Maximum Sensor Format:
2.74	Pixel Size (µm):
Threading & Mounting	
M72 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details


- High Resolution Telecentric Lens for Measurement and Gauging
- Up to 5 MegaPixels, 3.45µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.06X to 1X

TECHSPEC® GoldTL™ Telecentric Lenses were designed specifically for machine vision and metrology applications. The unique focusable design allows for working distance adjustment, while still providing <0.2° telecentricity. These lenses also feature high resolutions, low distortions, and are available for 1/2" or 2/3" sensors. TECHSPEC® GoldTL™ Telecentric Lenses have a front filter thread for easy integration of [color filters](#), [polarizers](#) or other mounted components. Both the iris and focusing adjustment positions can be fixed by set screws to remain secure in high vibration environments.


Technical Information




#58-258, 0.18X ½" GoldTL™ Telecentric Lens, Distortion Plot



#58-258, 0.18X ½" GoldTL™ Telecentric Lens, Relative Illumination Plot




#58-258, 0.18X ½" GoldTL™ Telecentric Lens, Telecentricity Plot



#58-258, 0.18X ½" GoldTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 165mm Working Distance, f6



#58-258, 0.18X ½" GoldTL™ Telecentric Lens, Depth of Field Plot, 165mm Working Distance, f6



#58-258, 0.18X ½" GoldTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 165mm Working Distance, f10



#58-258, 0.18X ½" GoldTL™ Telecentric Lens, Depth of Field Plot, 165mm Working Distance, f10

Stock No.	A	B	C	D	E	F	G
#56-024	88mm	16mm	34mm	94mm	120mm	101.6mm	50mm
#56-025	85mm	17.5mm	32.5mm	91mm	120mm	101.6mm	48.5mm
#56-026	103mm	—	39.5mm	107mm	103mm	90mm	55.5mm
#56-027	134mm	—	55mm	148mm	134mm	122mm	81mm

