

TECHSPEC[®] 0.136X, 1" C-Mount TitanTL[®] Telecentric Lens



TitanTL[®] Telecentric Lens

Stock #34-011 3-4 DAYS



1



£3,378.75

ADD TO CART

Qty 1+

£3,378.75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
47.2mm

Horizontal Field of View, 2/3" Sensor:
64.8mm

Weight (kg):
6.88

Horizontal Field of View, 1" Sensor:
94.2mm (Horizontal)

Numerical Aperture NA, Object Side:

0.0062
Resolution, Image Space: 50 lp/mm @ 40% (MTF, open)
Number of Elements (Groups): 6 (4)
Note: TitanTL®
Horizontal Field of View, 1/1.8" Sensor: 53.0mm
Type: Telecentric Lens
Primary Magnification PMAG: 0.136X
Maximum Sensor Format: 1"
Working Distance (mm): 223
Mount: C-Mount
Aperture (f/#): f/11 - f/22
Coating: λ/4 MgF ₂
Depth of Field (mm): ±30.7mm (20% @ 20 lp/mm, open)
FOV @ Max Sensor Format, H x V (mm): 94.1 x 70.6
Rear Filter Diameter (mm): 25.4
Typical Distortion @ 520nm (%): <0.13
Typical Telecentricity @ 520nm (°): <0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View