

## 0.19 - 20µm, 15J, Pyroelectric Energy Detector



0.19 - 20µm, 15J, Pyroelectric Energy Detector

Stock #78-469 **1 In Stock**

- 1 + £2,464.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	£2,464.00 each
Qty 5+	£2,220.00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

QE50LP-H-MB-INT-D0 **Model Number:**

Heatsink **Cooling Method:**

1 of (#15-267) is included **Note:**

15 **Maximum Incident Energy (J):**

Integra (Integrated)

**Compatible Meters:**

## Physical & Mechanical Properties

75 x 75 x 44 **Dimensions (mm):**

338 **Weight (g):**

0.34 **Weight (kg):**

50 x 50 **Active Area (mm):**

## Optical Properties

190 - 20000 **Wavelength Range (nm):**

0.19 - 20 **Wavelength Range (µm):**

## Sensor

Pyroelectric **Type of Sensor:**

## Electrical

20,000 **Maximum Incident Beam Power (mW):**

20 **Maximum Incident Beam Power (W):**

0.6 **Maximum Incident Energy Density (J/cm<sup>2</sup>, 10ns Pulses):**

10 µJ **Noise Level:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Photodetectors, Thermopiles, and Pyroelectric Detectors Available
- Various Active Area Sizes Across a Wide Range of Sensitivities
- [Meterless](#) and [Wireless](#) Detectors Also Available

Gentec-EO Integra USB Power and Energy Detectors combine a power meter and detector in one convenient package while providing fast response times and accurate measurements for beam analysis. These detectors are designed with a USB connector for easy connection to a PC or other acquisition system and include user-friendly software allowing for control via PC or serial commands. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Gentec-EO Integra USB Power and Energy Detectors can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts. These detectors are ideal for laser energy measurement, thermal imaging, and remote sensing applications.