

**TECHSPEC® 0.191X, 4/3" C-Mount TitanTL® Telecentric Lens**



TitanTL® Telecentric Lens

Stock **#34-016** 3-4 DAYS

- 1 + **£3,378.75**

ADD TO CART

Qty 1+

£3,378.75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Horizontal Field of View, 1/2" Sensor:**  
33.5mm

**Horizontal Field of View, 2/3" Sensor:**  
46.1mm

**Weight (kg):**  
3.58

**Horizontal Field of View, 1" Sensor:**  
67.1mm

**Numerical Aperture NA, Object Side:**

|                                                               |
|---------------------------------------------------------------|
| 0.0087                                                        |
| <b>Resolution, Image Space:</b><br>50 lp/mm @ 35% (MTF, open) |
| <b>Horizontal Field of View, 4/3" Sensor:</b><br>90.6mm       |
| <b>Number of Elements (Groups):</b><br>6 (4)                  |
| <b>Note:</b><br>TitanTL®                                      |
| <b>Horizontal Field of View, 1/1.8" Sensor:</b><br>37.7mm     |
| <b>Type:</b><br>Telecentric Lens                              |
| <b>Primary Magnification PMAG:</b><br>0.191X                  |
| <b>Maximum Sensor Format:</b><br>4/3"                         |
| <b>Working Distance (mm):</b><br>221                          |
| <b>Mount:</b><br>C-Mount                                      |
| <b>Aperture (f/#):</b><br>f/11 - f/22                         |
| <b>Coating:</b><br>λ/4 MgF <sub>2</sub>                       |
| <b>Depth of Field (mm):</b><br>±15.2mm (20% @ 20 lp/mm, open) |
| <b>FOV @ Max Sensor Format, H x V (mm):</b><br>94.2 x 70.7    |
| <b>Rear Filter Diameter (mm):</b><br>25.4                     |
| <b>Typical Distortion @ 520nm (%):</b><br><0.11               |
| <b>Typical Telecentricity @ 520nm (°):</b><br><0.1            |
| <b>Lens Wavelength Range:</b><br>VIS                          |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |