

0.19 - 20μm, 3W, Thermopile Power Detector



0.19 - 20μm, 3W, Thermopile Power Detector

Stock **#78-464** NEW **1 In Stock**

-

1

+

£1,692⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£1,692.00 each
Qty 5+	£1,520.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

	Maximum Incident Energy Density (J/cm², 10ns Pulses):
1	

General	
Model Number:	XLP12-3S-H2-INT-D0
Cooling Method:	Convection

Compatible Meters:

Integra (Integrated)	
Physical & Mechanical Properties	
73 x73 x20	Dimensions (mm):
310	Weight (g):
0.31	Weight (kg):
12	Active Area (mm):
Optical Properties	
190 - 20000	Wavelength Range (nm):
0.19 - 20	Wavelength Range (µm):
Sensor	
Thermopile	Type of Sensor:
Electrical	
3,000	Maximum Incident Beam Power (mW):
3	Maximum Incident Beam Power (W):
1,000	Maximum Incident Power Density (W/cm²):
1	Maximum Incident Power Density (kW/cm²):
0.5 µW	Noise Level:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Photodetectors, Thermopiles, and Pyroelectric Detectors Available
- Various Active Area Sizes Across a Wide Range of Sensitivities
- [Meterless](#) and [Wireless](#) Detectors Also Available

Gentec-EO Integra USB Power and Energy Detectors combine a power meter and detector in one convenient package while providing fast response times and accurate measurements for beam analysis. These detectors are designed with a USB connector for easy connection to a PC or other acquisition system and include user-friendly software allowing for control via PC or serial commands. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Gentec-EO Integra USB Power and Energy Detectors can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts. These detectors are ideal for laser energy measurement, thermal imaging, and remote sensing applications.