

TECHSPEC® 0.20X SilverTL™ Telecentric Lens



0.20X Magnification



Stock **#63-073** ☐ In Stock

- 1 +

£956.25

ADD TO CART

Qty 1+

£956.25

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
188.00

Horizontal Field of View, 1/2" Sensor:
32mm

Filter Thread:
M58 x0.75 (Female)

Maximum Diameter (mm):

60.00
Weight (g): 346
Horizontal Field of View, 1/3" Sensor: 24mm
Numerical Aperture NA, Object Side: 0.016
Working Distance Tolerance (mm): ±3
Stock No. of Mounting Clamp: #56-871 Sold Separately
Resolution, Image Space MTF @ f/10: >40% @ 40 lp/mm
Number of Elements (Groups): 6 (5)
Note: SilverTL™
Horizontal Field of View, 1/1.8" Sensor: 35.9mm
Typical Telecentricity @ 588nm (°): <0.055
Typical Distortion @ 588nm (%): <0.150
Type: Telecentric Lens
Primary Magnification PMAG: 0.2X
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 164.00
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Construction: Anodized Aluminum
Depth of Field (mm): ±12.9 at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 36.0 x 27.0
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View