

0.22 NA VIS/NIR Patchcord 200 Micron Fiber w/ FC Connector



Stock #23-708 1 In Stock

-

1

+

£153^{.60}

ADD TO CART

Volume Pricing	
Qty 1-4	£153.60 each
Qty 5-10	£138.40 each
Qty 11-24	£123.20 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Patchcord	Type:
Multimode	Fiber Cable Type:

Physical & Mechanical Properties

1.5	Length (m):
-----	-------------

200	Core Diameter (µm):
PVC MONOCOIL (0.112" OD)	Jacket Material:
Optical Properties	
Nylon	Coating Type:
0.22	Numerical Aperture NA:
VIS-IR	Wavelength:
Hardware & Interface Connectivity	
FC/PC	Connector:
Environmental & Durability Factors	
-40 to +100	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- UV/MS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

Technical Information

