

[See all 19 Products in Family](#)

## 0.22 NA VIS/NIR Patchcord 200 Micron Fiber w/ SMA Connector



Stock #23-692 **5 In Stock**

⊖ 1 ⊕ £157<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	£157.60 each
Qty 5-10	£141.60 each
Qty 11-24	£123.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Patchcord **Type:**  
Multimode **Fiber Cable Type:**

### Physical & Mechanical Properties

1.5 **Length (m):**

200 Core Diameter ( $\mu\text{m}$ ):

PVC MONOCOIL (0.112" OD) Jacket Material:

## Optical Properties

Nylon Coating Type:

0.22 Numerical Aperture NA:

VIS-IR Wavelength:

## Hardware & Interface Connectivity

SMA905 Connector:

## Environmental & Durability Factors

-40 to +100 Operating Temperature ( $^{\circ}\text{C}$ ):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

## Product Details

- UV/MS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000 $\mu\text{m}$ , these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

## Technical Information

