

[See all 19 Products in Family](#)

0.22 NA VIS/NIR Patchcord 50 Micron Fiber w/ SMA Connector



Stock #23-704 **1 In Stock**

- 1 + £157.⁶⁰

ADD TO CART

Volume Pricing

Qty 1-4	£157.60 each
Qty 5-10	£141.60 each
Qty 11-24	£126.40 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Patchcord **Type:**
Multimode **Fiber Cable Type:**

Physical & Mechanical Properties

1.5 **Length (m):**

50 Core Diameter (µm):

PVC MONOCOIL (0.112" OD) Jacket Material:

Optical Properties

Nylon Coating Type:

0.22 Numerical Aperture NA:

VIS-IR Wavelength:

Hardware & Interface Connectivity

SMA905 Connector:

Environmental & Durability Factors

-40 to +100 Operating Temperature (°C):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

Product Details

- UV/MS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

Technical Information

