

0.22" Travel, XYZ Axes, Extended Travel, Micro Series (A)



Stock **#56-421** 1 In Stock

-

1

+

£800⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£800.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
English	Type:
Without Covered Rails	Note:

Physical & Mechanical Properties

Linear (X-Y-Z)	Type of Movement:
----------------	-------------------

Ball Bearing	Guide System:
Center Drive	Drive Orientation:
11.2 x 26.2	Stage Size (mm):
5.6	Travel (mm):
0.22	Travel (inches):
0.155" (3.9mm) Thru with 8-32 TPI Threaded	Center Hole:
Aluminum Body, Stainless Steel Rails	Construction:
0.25	Load Capacity, Normal (kg):
0.44 x 1.03	Stage Size (inches):
1.5	Straight Line Accuracy (µm):
7.5	Weight (g):

Optical Properties

0.01	Wobble (mrad):
------	----------------

Hardware & Interface Connectivity

Fine Screw (80 Pitch)	Type of Drive:
-----------------------	----------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Two Micro Sizes Available
- Versions with Covered Rails
- Three Travel Selections
- X, XY, and XYZ Axis Mbdels

These stages are a dimensional breakthrough and the smallest positioners available today. Positive spring loaded carriage provides precise, smooth motion with no backlash. Straight line accuracy under 2 microns. Features fine 80 TPI lead screw drive. The larger series, Stage Size B, are for longer travel, higher load applications. Fully metric compatible clearance holes. Covered Rail versions are slightly wider, but offer protection for the guide rails. Accessories allow for mounting our precision pinholes for spatial filtering applications. Anodized aluminum construction with stainless rails.

Technical Information

