

TECHSPEC® 0.377X, 4/3" C-Mount TitanTL® Telecentric Lens



TitanTL® Telecentric Lens

Stock **#34-015** 3-4 DAYS

- 1 + **£1,785.00**

ADD TO CART

Qty 1+

£1,785.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
17.0mm

Horizontal Field of View, 2/3" Sensor:
23.3mm

Filter Thread:
M72 x0.75 (Female)

Weight (kg):
0.85

Horizontal Field of View, 1" Sensor:

34.0mm
Numerical Aperture NA, Object Side: 0.0171
Resolution, Image Space: 50 lp/mm @ 21% (MTF, open)
Horizontal Field of View, 4/3" Sensor: 45.9mm
Number of Elements (Groups): 6 (4)
Note: TitanTL®
Horizontal Field of View, 1/1.8" Sensor: 19.1mm
Type: Telecentric Lens
Primary Magnification PMAG: 0.377X
Maximum Sensor Format: 4/3"
Working Distance (mm): 110
Mount: C-Mount
Aperture (f/#): f/11 - f/22
Coating: N4 MgF ₂
Depth of Field (mm): ±4.0mm (20% @ 20 lp/mm, open)
FOV @ Max Sensor Format, H x V (mm): 47.7 x 35.8
Rear Filter Diameter (mm): 25.4
Typical Distortion @ 520nm (%): <0.05
Typical Telecentricity @ 520nm (°): <0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View