

0.50 NA, 4.5mm FL, HOYA Molded Glass Aspheric Lens

See More by [Hoya](#)



HOYA Molded Glass Aspheric Lenses

Stock **#13-588** 3-4 DAYS

-

1

+

£85.00

ADD TO CART

Qty 1-10

£85.00

Qty 11+

£67.15

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
6.38 +0.00/-0.02

Effective Focal Length EFL (mm):
4.50 @ 780nm

Numerical Aperture NA:
0.50

Substrate: M-LaF81
Aspheric Design Wavelength (nm): 780
Coating: BBAR (680-880nm)
Coating Specification: R_{avg} <1% @ 680 - 880nm (typical)
Center Thickness CT (mm): 2.80
f/#: 0.71
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 680 - 880
Working Distance (mm): 2.16
Conjugate Distance: 0
Transmitted Wavefront, RMS @ 632.8nm: 0.04λ
Model Number: AH10_Z

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View