

[See all 28 Products in Family](#)

0.5 OD, 50mm Sq., Precision Anti-Reflection (AR) Coated Absorptive ND Filter



Precision Absorptive Neutral Density (ND) Filters

Stock **#16-056** **3 In Stock**

⊖ 1 ⊕ £200⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	£200.80 each
Qty 11-25	£177.60 each
Qty 26-49	£163.20 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Neutral Density Filter **Type:**

Physical & Mechanical Properties

50.00 x 50.00 +0.00/-0.25 **Dimensions (mm):**

Length (mm):

50.00

2.11 (nominal)

Thickness (mm):

50.00

Width (mm):

90

Clear Aperture (%):

<30

Parallelism (arcsec):

Optical Properties

Optical Density OD (Average):
0.5 ± 10% @ 550nm

Glass/Filter Number:
SCHOTT NG5

Substrate:
ND Filter Glass

Coating:
BBAR (450-700nm)

Index of Refraction (n_d):
1.50

Surface Quality:
80-50

Transmission (%):
31.62

Blocking Wavelength Range (nm):
400 - 700

Transmitted Wavefront, P-V:
λ/4

Coating Specification:
R_{avg} ≤ 1.0% @ 450 - 700nm @ 0°

Material Properties

Transformation Temperature (°C):
474

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View


REACH 241:
Compliant

Product Details

- λ/4 Transmitted Wavefront Distortion
- AR Coated for 450 - 700nm
- Optical Densities from 0.1 to 4.0 Available
- **Absorptive Neutral Density (ND) Filters** Also Available

Precision Anti-Reflection (AR) Coated Absorptive Neutral Density (ND) Filters feature SCHOTT NG Colored Glass substrates that are polished to achieve a transmitted wavefront distortion (TWFD) specification of λ/4. These filters are coated on both surfaces with an anti-reflection (AR) coating from 450 - 700nm, reducing back reflections and enabling filter stacking with less losses and artifacts. Precision Anti-Reflection (AR) Coated Absorptive Neutral Density (ND) Filters are available with optical densities from 0.1 to 4.0 and can be stacked together to achieve custom optical densities to meet application requirements. These neutral density filters are available in 25mm diameter or 50mm square sizes and are ideal for machine vision, imaging, or low power laser applications.

Technical Information





Compatible Mounts

;