

0.50" Travel, 0.001" Grad, Micrometer Drive Mech



Drive Mechanisms

Stock #58-660 **14 In Stock**

⊖ 1 ⊕ £154⁴⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-9 | £154.40 each |
| Qty 10-24 | £138.96 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**
PARKER-HANNIFIN **Manufacturer:**

Physical & Mechanical Properties

0.5 **Travel (inches):**

| | |
|--------------|----------------------------------|
| 0.001 | Graduation (inches): |
| 9.5 | Stem Diameter (mm): |
| Plain/Flat | Stem/Spindle: |
| 9.5 | Stem Length (mm): |
| 6.6 (0.26") | Spindle Diameter (mm): |
| 6.35 (0.25") | Min. Spindle Length (mm): |
| 13.7 (0.54") | Max. Diameter (mm): |
| 60.5 (2.38") | Overall Length (mm): |

Hardware & Interface Connectivity

| | |
|--------------------|-----------------------|
| English Micrometer | Type of Drive: |
|--------------------|-----------------------|

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential. Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

