

[See all 76 Products in Family](#)

LightPath 354105 | 7.2mm Dia., 0.56 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-146** **8 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ £71²⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£71.20 each
Qty 11-49	£64.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Thickness: 0.25 (t) (mm)
Material: BK7

Compatible Window:

354105

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
7.20 ±0.020

Clear Aperture CA (mm):
6

Edge Thickness ET (mm):
1.29

Center Thickness CT (mm):
2.94 ±0.03

Bevel:
Protective as needed

Distance from Window to Lens (D) (mm):
3.091

Optical Properties

Effective Focal Length EFL (mm):
5.50 @ 633nm

Numerical Aperture NA:
0.60

Substrate:
[D-ZK3](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
633

Coating:
BBAR (600-1050nm)

Coating Specification:
R_{abs} <1.0% @ 600 - 1050nm

Surface Quality:
40-20

f#:
0.89

Wavelength Range (nm):
600 - 1050

Working Distance (mm):
3.7

Conjugate Distance:
Infinite

Transmitted Wavefront Error (λ, RMS):
< 0.07

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



