

0.6 OD, 25mm Dia., Precision Anti-Reflection (AR) Coated Absorptive ND Filter



Precision Absorptive Neutral Density (ND) Filters

Stock **#16-057** **5 In Stock**

-

1

+

£93⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£93.60 each
Qty 11-25	£84.80 each
Qty 26-49	£76.40 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Neutral Density Filter	Type:
Physical & Mechanical Properties	
25.00	Diameter (mm):
	Thickness (mm):

2.54 (nominal)	
90	Clear Aperture (%):
<30	Parallelism (arcsec):
Optical Properties	
Optical Density OD (Average):	
0.6 ±10% @ 550nm	
Glass/Filter Number:	
SCHOTT NG5	
Substrate: □	
ND Filter Glass	
Coating:	
BBAR (450-700nm)	
Index of Refraction (n _d):	
1.50	
Surface Quality:	
80-50	
Transmission (%):	
25.12	
Blocking Wavelength Range (nm):	
400 - 700	
Transmitted Wavefront, P-V:	
λ/4	
Coating Specification:	
R _{avg} ≤1.0% @ 450 - 700nm @ 0°	

Material Properties	
Transformation Temperature (°C):	
474	


Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	



Product Details

- λ/4 Transmitted Wavefront Distortion
- AR Coated for 450 - 700nm
- Optical Densities from 0.1 to 4.0 Available
- Absorptive Neutral Density (ND) Filters Also Available

Precision Anti-Reflection (AR) Coated Absorptive Neutral Density (ND) Filters feature SCHOTT NG Colored Glass substrates that are polished to achieve a transmitted wavefront distortion (TWFD) specification of λ/4. These filters are coated on both surfaces with an anti-reflection (AR) coating from 450 - 700nm, reducing back reflections and enabling filter stacking with less losses and artifacts. Precision Anti-Reflection (AR) Coated Absorptive Neutral Density (ND) Filters are available with optical densities from 0.1 to 4.0 and can be stacked together to achieve custom optical densities to meet application requirements. These neutral density filters are available in 25mm diameter or 50mm square sizes and are ideal for machine vision, imaging, or low power laser applications.

Technical Information





Compatible Mounts

;