


[See all 20 Products in Family](#)

TECHSPEC[®]

0° AOI, 25.0mm Diameter, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock **#64-437** **6 In Stock**

-

1

+

£47⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£47.60 each
Qty 10-25	£42.80 each
Qty 26-49	£40.80 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Cold Mirror

Type:

Physical & Mechanical Properties

25.00

Diameter (mm):


Thickness (mm):

3.30 ±0.2	
	Dimensional Tolerance (mm):
+0.0/-0.2	
Optical Properties	
Longpass Filter	Transmission (%):
Dielectric	Coating Type:
	Coating:
Cold Mirror, 0°	
4 - 6λ	Surface Flatness (P-V):
400 - 1150	Wavelength Range (nm):
BOROFLOAT®	Substrate: □
0	Angle of Incidence (°):
Coating Specification: R _{avg} ≥95% @400 - 690nm and T _{avg} ≥90% @ 750 - 1200nm AR Coating: R _{avg} <1% @ 700 - 1150nm	
80-50	Surface Quality:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- >95% Reflection from 400 - 690nm
 - >90% Transmission from 750 - 1200nm
 - Optimized for 0° or 45° Angle of Incidence
- TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

Technical Information



Quote Your Size

Compatible Mounts

