

**TECHSPEC® 0° AOI, 25.0mm Diameter, Cold Mirror**



TECHSPEC High Performance Cold Mirrors

Stock **#64-437** **5 In Stock**

⊖ 1 ⊕ £47<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | £47.60 each                   |
| Qty 10-25      | £42.80 each                   |
| Qty 26-49      | £40.80 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cold Mirror **Type:**

**Physical & Mechanical Properties**

25.00 **Diameter (mm):**

**Thickness (mm):**

3.30 ±0.2

Dimensional Tolerance (mm):

+0.0/-0.2

## Optical Properties

Longpass Filter **Transmission (%)**:

Dielectric **Coating Type**:

Cold Mirror, 0° **Coating**:

4 - 6λ **Surface Flatness (P-V)**:

400 - 1150 **Wavelength Range (nm)**:

**BOROFLOAT®** **Substrate**: □

0 **Angle of Incidence (°)**:

**Coating Specification**:  
R<sub>avg</sub> ≥95% @ 400 - 690nm and T<sub>avg</sub> ≥90% @ 750 - 1200nm  
AR Coating: R<sub>avg</sub> <1% @ 700 - 1150nm

80-50 **Surface Quality**:

## Regulatory Compliance

**Compliant** **RoHS 2015**:

**View** **Certificate of Conformance**:



**Compliant** **Reach 247**:

## Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

## Technical Information



**Quote Your Size**

**Compatible Mounts**

