


## 0° AOI 25mm Dia, Cold Mirror



Stock #43-844 CLEARANCE **20+ In Stock**

1  £12<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£12.20 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Cold Mirror **Type:**

#### Physical & Mechanical Properties

25.00 **Diameter (mm):**

3.30 **Thickness (mm):**

±0.25 **Dimensional Tolerance (mm):**

## Optical Properties

Dielectric **Coating Type:**

Cold Mirror, 0° **Coating:**

4 - 6λ **Surface Flatness (P-V):**

425 - 1200 **Wavelength Range (nm):**

**BOROFLOAT®** **Substrate:** □

0.00 **Angle of Incidence (°):**

**Coating Specification:**  
R<sub>avg</sub> >90% @ 425 - 675nm  
T<sub>avg</sub> >85% @ 800 - 1200nm

80-50 **Surface Quality:**

## Regulatory Compliance



[View](#) **Certificate of Conformance:**

## Product Details

- 0° and 45° Angle of Incidence Options Available
- Reflects 90% of Visible Light
- Transmits 80% of the NIR and IR

These Cold Mirrors have a 0° and 45° angle of incidence and are ideal for decreasing the undesirable heat caused by infrared radiation. A multi-layer dielectric coating reflects 90% of visible light while transmitting over 80% of the NIR and IR. Cold Mirrors function satisfactorily with resistance to damage from ambient temperatures of -45°C to +232°C and are ideal for projection systems, where heat build-up can lead to system damage. Made of BOROFLOAT® glass, these Cold Mirrors can be cut to the desired size for any application.

## Technical Information



## Compatible Mounts