

[See all 12 Products in Family](#)

# 1-1.75mm, 24-14TPI, Screw Thread Micrometer Anvil/Tip Set

See More by [Mitutoyo](#)



Stock **#78-308** **1 In Stock**

-

1

+

£80<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £80.80 each                   |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

| Product Downloads           |               |
|-----------------------------|---------------|
|                             |               |
| General                     |               |
| 24 - 14 TPI, 1 - 1.75mm     | Range:        |
| V Anvil and Conical Spindle | Type:         |
| 126-803                     | Model Number: |
| Regulatory Compliance       |               |

## Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6”
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mike Micrometer features interchangeable anvils ranging from 0-1” for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.