


TECHSPEC®

1" Dia. λ /10 Fused Silica Dual Surface Flat



Stock **#43-424** ☒ In Stock

-

1

+

£174.25

ADD TO CART

Qty 1+

£174.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
 λ /10

Abbe Number (v_d):
67.8

Coating:
Uncoated

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):
0.52 (+5 to +35°C)

0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Diameter (mm): 25.40 ±1.0
Thickness (mm): 12.70 ±1.5
Diameter (inches): 1.00 ±0.04
Thickness (inches): 0.50 ±0.06
Clear Aperture CA (mm): 22.90
Construction: Dual Surface
Density (g/cm³): 2.20
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcmin): <3
Poisson's Ratio: 0.16
Substrate: Fused Silica
Surface Quality: 60-40
Type: Interferometry Window
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View