

[See all 34 Products in Family](#)

1 mW, 1550nm Alignment Laser Diode



Red and IR Alignment Laser Diode

Stock **#29-127** **1 In Stock**

£764⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£764.00 each
Qty 10+	£687.60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Laser Class - CDRH:
 IIIb

Physical & Mechanical Properties

Length (mm):
 36.00

Optical Properties

Wavelength (nm):
1,550.00

Wavelength Tolerance (nm):
±10

Beam Diameter (mm):
3.5 typical

Beam Divergence (mrad):
<1.0

Color:
Infrared

Electrical

Output Power (mW):
1

Modulation Frequency (kHz):
0 - 10

Hardware & Interface Connectivity

Operating Voltage (V):
5

Power Supply:
Power Supply Required and Sold Separately:
USA: [#73-818](#)
Europe: [#73-818](#)
Japan: [#13-640](#)
Korea: [#33-770](#)
China: [#73-818](#)

Environmental & Durability Factors

Operating Temperature (°C):
10 to 35

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Focus Adjustable
- TTL Modulation up to 10kHz
- 635nm, 780nm, 808nm, 850nm, and 980nm Wavelength Options

Red and IR Alignment Laser Diodes are available in output powers from 1 to 100mW at 635nm, 780nm, 808nm, 850nm, and 980nm wavelengths. These low cost laser diode modules combine drive electronics and beam collimating optics, making them ideal for OEM integration applications. Red and IR Alignment Laser Diodes feature TTL Modulation up to 10kHz and are best utilized in alignment applications or systems with simple detectors.

Note: Power supply and mounting bracket are sold separately.