

[See all 4 Products in Family](#)

## Siemens Star Target, 4" x 4", 120 Sectors Photo Paper



Photo Paper Star Target

Stock #46-246 [CONTACT US](#)

⊖ 1 ⊕ £137<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	£137.60 each
Qty 5+	£130.96 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Emulsion Coated

Note:

No

NIST Certification:

### Physical & Mechanical Properties

0.033 - 0.818

Line Width (mm):

120.00	<b>Number of Sectors:</b>
62.5	<b>Pattern Diameter (mm):</b>
4 x 4 ±0.004	<b>Dimensions (inches):</b>
0.20 ±nominal	<b>Thickness (mm):</b>

## Optical Properties

0.6112 - 15.28	<b>Frequency (lp/mm):</b>
Photo Paper	<b>Substrate:</b> <input type="checkbox"/>
>1.6	<b>Optical Density OD (Average):</b>
3°	<b>Wedge Angle (°):</b>
2.5	<b>Unresolved Core Diameter (mm):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 235:</b>

## Product Details

- Ideal for Detection of Focus Errors and Astigmatism
- Frequency Range at Target Center (lp/mm) 7.14 - 229.2
- Available on White Photographic Paper or Chrome on Glass

Star Targets are ideal for identifying focus errors, astigmatism, and other aberrations existing in an imaging system. Our 60mm diameter ([#58-832](#) and [#58-833](#)) targets feature an unresolved core of 100µm and are ideal for high-resolution or high magnification imaging systems. Both targets are chrome on glass. Star Targets, in the 4" x 4" size, are available as chrome on glass ([#46-247](#)) or photo paper ([#46-246](#)), feature an unresolved core of 2.7mm, and are designed for mid- to low-range spatial frequencies common in macro imaging systems. These targets have a frequency range at target center (lp/mm) of 7.14-229.2.