

[See all 4 Products in Family](#)

# Siemens Star Target, 4" x 4", 120 Sectors Photo Paper



Photo Paper Star Target

Stock **#46-246** **17 In Stock**

-

1

+

£137<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | £137.60 each                  |
| Qty 5+         | £130.96 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Emulsion Coated

Note:

No

NIST Certification:

Physical & Mechanical Properties

0.033 - 0.818

Line Width (mm):

|               |                        |
|---------------|------------------------|
| 120.00        | Number of Sectors:     |
| 62.5          | Pattern Diameter (mm): |
| 4 x 4 ±0.004  | Dimensions (inches):   |
| 0.20 ±nominal | Thickness (mm):        |

|                    |                                |
|--------------------|--------------------------------|
| Optical Properties |                                |
| 0.6112 - 15.28     | Frequency (lp/mm):             |
| Photo Paper        | Substrate:                     |
| >1.6               | Optical Density OD (Average):  |
| 3°                 | Wedge Angle (°):               |
| 2.5                | Unresolved Core Diameter (mm): |

|                           |                             |
|---------------------------|-----------------------------|
| Regulatory Compliance     |                             |
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 235:                  |

## Product Details

- Ideal for Detection of Focus Errors and Astigmatism
- Frequency Range at Target Center (lp/mm) 7.14 - 229.2
- Available on White Photographic Paper or Chrome on Glass

Star Targets are ideal for identifying focus errors, astigmatism, and other aberrations existing in an imaging system. Our 60mm diameter ([#58-832](#) and [#58-833](#)) targets feature an unresolved core of 100µm and are ideal for high-resolution or high magnification imaging systems. Both targets are chrome on glass. Star Targets, in the 4" x 4" size, are available as chrome on glass ([#46-247](#)) or photo paper ([#46-246](#)), feature an unresolved core of 2.7mm, and are designed for mid- to low-range spatial frequencies common in macro imaging systems. These targets have a frequency range at target center (lp/mm) of 7.14-229.2.