

TECHSPEC® 10" Diameter x 60" FL Enhanced Aluminum, Parabolic Mirror



Stock #32-274-533 [CONTACT US](#)

⊖ 1 ⊕ £2,158¹¹

ADD TO CART

Volume Pricing	
Qty 1-2	£2,158.11 each
Qty 3-9	£1,834.17 each
Qty 10-24	£1,742.25 each
Need More?	Request Quote

¹¹ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Parabolic Mirror **Type:**

Physical & Mechanical Properties

10.0 +0.06/-0 Diameter (inches):

254.00 +1.5/-0 Diameter (mm):

Ground Back Surface:

229 Clear Aperture CA (mm):

1.75 Edge Thickness ET (inches):

44.50 Edge Thickness ET (mm):

Optical Properties

BOROFLOAT®SUPREMAX® Substrate:

±1.5 Focal Length Tolerance (%):

60-40 Surface Quality:

λ/8 Surface Accuracy:

60.0 Effective Focal Length EFL (inches):

1,524.00 Effective Focal Length EFL (mm):

3,048.00 Radius of Curvature (mm):

f/6 Aperture (f#):

Enhanced Aluminum (450-650nm) Coating:

R_{avg} >95% @ 450 - 650nm Coating Specification:

Metal Coating Type:

0.45 - 0.65 Wavelength Range (μm):

450 - 650 Wavelength Range (nm):

0.2 J/cm² @ 532nm, 10ns Damage Threshold, Reference:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

PRODUCT DETAILS

- λ/8 Surface Accuracy
- Wide Range of Sizes up to 412.8mm Diameter
- Variety of Coating Options Offered

TECHSPEC® Precision Parabolic Mirrors are available in sizes ranging from 3" (76.2mm) to 16.25" (412.8mm) and are ideal for a wide range of applications. These parabolic mirrors are offered with protected aluminum, enhanced aluminum or protected gold coatings. Uncoated substrates are also available.

TECHSPEC® Precision Parabolic Mirrors deliver exceptional optical performance for high-precision focusing and collimation across a wide wavelength range. These parabolic mirrors feature λ/8 surface accuracy and 60-40 surface quality, minimize aberrations and scattering, and ensure high reflectivity and tight focus in demanding laser, imaging, and illumination systems. They offer excellent reflectance from visible to infrared regions and are available with protected aluminum, enhanced aluminum, protected gold coatings, or uncoated. Designed with BOROFLOAT® substrates for superior thermal stability, they perform well for applications in aerospace, spectroscopy, and optical instrumentation where precise beam control is critical.

FAQ(s)

Which coating options are available for these parabolic mirrors?

Coating options include protected aluminum, enhanced aluminum for high visible reflectivity, protected gold for infrared use, and uncoated versions.

What materials are used for the mirror substrates?

BOROFLOAT® glass provides excellent thermal stability and mechanical durability, especially in temperature-sensitive environments.


In what types of applications are these parabolic mirrors typically used?

They are ideal for laser systems, optical instruments, spectroscopy setups, aerospace applications, beam collimation or focusing assemblies, and more.

How large are the available diameters for the Precision Parabolic Mirrors?

Mirror sizes range from 3 inches (76.2mm) to 16.25 inches (412.8mm), offering a wide selection for different optical design needs.

TECHNICAL INFORMATION



COATING CURVES
