See all 24 Products in Family

10mW, 520nm DPSS Pointing Laser

DPSS Pointing Lasers

Stock **#29-132** **1 In Stock**

- 1 + **£203**.20

ADD TO CART

Volume Pricing	
Qty 1-9	**£203.20** each
Qty 10+	**£183.20** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Class - CDRH:
IIIb

Physical & Mechanical Properties

Length (mm):
36.00

Optical Properties

Spatial Mode:	
TEM_{00}	
Wavelength (nm):	
520.00 ±10	
Beam Diameter (mm):	
3.5 Typical	
Beam Divergence (mrad):	
<1 Typical	
Color:	
Green	

Electrical

Output Power (mW):	
10	
Modulation Frequency (kHz):	
0 - 10	

Hardware & Interface Connectivity

Operating Voltage (V):	
7	

Environmental & Durability Factors

Operating Temperature (°C):	
23 to 27	

Regulatory Compliance

Certificate of Conformance:	
View	

Product Details

- TTL Modulation up to 10kHz
- Transverse Mode TEM_{00}
- Blue, Green, Yellow, and IR Output Wavelengths
- TEC or Heatsink Required for Operation (**Sold Separately**)

DPSS Pointing Lasers are diode pumped solid state lasers available in output powers ranging from 1 to 100mW. With their solid state design, these lasers offer excellent mode purity and low divergence, making them ideal for applications that require long projection distances. The turnkey design featuring integrated optics and electronics in a single package is suitable for a variety of plug and play operations. DPSS Pointing Lasers provide high brightness circular output beams and are ideal for many different OEM applications. TEC Controller or heatsink is required to maintain 23°C – 27°C operating temperature range.

Note: Power supplies, TEC Controller **(#19-476)**, Line Projection Heads (for 532nm - **#37-093**)(for 1064nm - **#37-097**), and mounting brackets (**#37-144**) are sold separately.

;